

ALPHA

8476UFX160P67 OH200 BRAKE-ASM

EAN 4031582380545
Order number 00064659



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Alpha
Housing type	Swivel castor with central , total lock
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	551.16 lb
Load capacity Static	1102.31 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	176 °F
Overall height	7.87 in
Overall width	3.9 in
Overall weight	4.14 lb

WHEEL

Body material	Polyamide
Tread material	Elastic tire, non-marking, vulcanized
Bearing	Precision ball bearing, sealed
Axle	Screwed with nut
Wheel color	Silver gray (RAL7001)
Threadguards	With threadguard
Diameter	6.3 in
Tread width	1.81 in
Body width	1.81 in
Hardness of tread (A)	63 Shore A

HOUSING

Material	Stainless steel, heavy
Fork shape	Broad
Swivel bearing	Two ball races
Color	Stainless steel
Offset	2.17 in
Swivel radius	5.65 in
Swivel interference	11.3 in
Dome diameter	3.78 in

FITTING

Fitting type	Plate with central locking
Plate length	6.93 in
Plate width	4.41 in
Plate hole length (Maximum)	3.05 in
Plate hole width (Maximum)	4.13 in
Plate hole diameter	0.51 in

ALPHA

8476UFX160P67 OH200 BRAKE-ASM

EAN 4031582380545
Order number 00064659



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

