

PRODUCT INFORMATION

MAXTECH

PNR400x90-Ø10x129 geel

EAN 4031582202373



Image may differ from the original product

PERFORMANCE

Roll Performance	● ○ ○ ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Maxtech
Type	Wheel
Load capacity at 1.8 mph	319.67 lb
Electric conductive	no
Stainless	no
Load capacity Static	639.34 lb
Overall weight	6.61 lb



BETTER MOBILITY. BETTER LIFE.

WHEEL

Tread hardness	soft
Body material	Polypropylene
Tread material	Polyurethane, foamed
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	15.75 in
Tread width	3.54 in
Axle hole diameter	0.39 in
Hub length	5.08 in
Hardness of tread (A)	55 Shore A

MAXTECH

PNR400x90-Ø10x129 geel

EAN 4031582202373



BETTER MOBILITY. BETTER LIFE.

Product Drawings

