

# ALPHA

8470IDG100P30-13 (DSG)

EAN 4031582382397



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ●

## CORE ATTRIBUTES

Product name	Alpha
Housing type	Swivel castor
Standard	EN12532 - Transport Equipment
Electric conductive	✓
Load capacity Static	352.74 lb
Temperature range (Minimum)	-22 °F
Temperature range (Maximum)	482 °F
Overall height	5.04 in
Overall weight	1.93 lb

## WHEEL

Body material	Aluminum
Tread material	Damping, heat resistant
Bearing	Dry bearing bush
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	3.94 in
Tread width	1.38 in
Hardness of tread (A)	75 Shore A

## HOUSING

Material	Stainless steel, heavy
Fork shape	Broad
Swivel bearing	Two ball races
Offset	1.61 in
Swivel radius	3.58 in
Swivel interference	7.17 in

## FITTING

Fitting type	Bolt hole
Bolt hole diameter	0.51 in

# ALPHA

8470IDG100P30-13 (DSG)

EAN 4031582382397



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

8470U0D100P30- $\phi$ 11

