

MAXTECH

UAK 050x20-Ø6,1

EAN 4031582322835



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Maxtech
Type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	110.23 lb
Electric conductive	no
Stainless	no
Load capacity Static	220.46 lb
Temperature range (Minimum)	-13 °F
Temperature range (Maximum)	176 °F
Overall weight	0.15 lb

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Cone ball bearing
Wheel color	Silver gray (RAL7001)
Threadguards	With threadguard
Diameter	1.97 in
Tread width	0.79 in
Axle hole diameter	0.24 in
Hub length	0.87 in
Body width	0.79 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

MAXTECH

UAK 050x20-Ø6,1

EAN 4031582322835

Order number 00008698
Product Drawings



BETTER MOBILITY. BETTER LIFE.

