

DURATECH

UOD160X40-Ø20 LM58 TFR

EAN 4031582485349



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Roller bearing, stainless
Diameter	160 mm
Tread width	40 mm
Axle hole diameter	20 mm
Hub length	58 mm
Hardness of tread (D)	75 Shore D

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Duratech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	400 kg
Load capacity Static	800 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall weight	0.57 kg

DURATECH

UOD160X40-Ø20 LM58 TFR

EAN 4031582485349



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

