

# PURETECH

PVO160X40-Ø20 HL58

EAN 4031582442366



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ○ ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ○ ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Puretech                      |
| Housing type                | Wheel                         |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 4 km/h     | 135 kg                        |
| Load capacity Static        | 270 kg                        |
| Temperature range (Minimum) | -20 °C                        |
| Temperature range (Maximum) | 60 °C                         |
| Overall weight              | 0.701 kg                      |

## WHEEL

|                       |                     |
|-----------------------|---------------------|
| Body material         | Polypropylene       |
| Tread material        | Solid rubber, black |
| Bearing               | Plain bearing       |
| Threadguards          | Without threadguard |
| Diameter              | 160 mm              |
| Tread width           | 40 mm               |
| Axle hole diameter    | 20 mm               |
| Hub length            | 58 mm               |
| Hardness of tread (A) | 85 Shore A          |

# PURETECH

PVO160X40-Ø20 HL58

EAN 4031582442366



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

