PRODUCT INFORMATION

MONO

A025PJI050L51-10 RAL7035

EAN 4031582359886



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●○○
Attrition	●●●○○
Corrosion Resistance	●●●●○

CORE ATTRIBUTES

Product Name	Mono
Type	Swivel castor with wheel brake
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	30 kg
Electric Conductive	No
Stainless	No
Load capacity Static	60 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall Height	72 mm
Overall weight	0.78 kg

HOUSING

Housing Material	Polypropylene
Fork shape	Closed
Swivel Bearing	Stem, swiveling
Housing Color	Light grey (RAL7035)
Offset	25 mm
Swivel radius	71.8 mm
Swivel interference	143.6 mm

WHEEL

Body material	Polypropylene
Tread Material Mix	Thermoplastic rubber
Bearing	Plain bearing with spacer tube
Threadguards	Without threadguard
Diameter	50 mm
Tread width	18 mm
Hardness of tread (A)	85 Shore A

FITTING

Fitting type	Blind hole for B10
Bolt hole diameter	10 mm

© Copyright 2026 TENTE International GmbH


MONO

A025PJI050L51-10 RAL7035

EAN 4031582359886

BETTER MOBILITY. BETTER LIFE.

Product Drawings



© Copyright 2026 TENTE International GmbH