

NOVATECH

ITP100x40-Ø15 HL40 Heavyduty



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Aluminum
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Wheel color	Honey yellow (RAL1005)
Threadguards	Without threadguard
Diameter	3.94 in
Tread width	1.57 in
Axle hole diameter	0.59 in
Hub length	1.57 in
Body width	1.57 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D
Suitable for	linde_jh_mic_yale

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	661.39 lb
Load capacity at 3.7 mph	529.11 lb
Electric conductive	no
Stainless	no
Load capacity Static	1322.77 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	140 °F
Overall weight	1.04 lb

Product Drawings

