

ALPHA STAINLESS

8470IDC100P30-13 TDK

EAN 4031582382174



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

HOUSING

Material fork	Stainless steel, heavy
Fork shape	Broad
Swivel bearing	Two ball races
Offset	41 mm
Swivel radius	91 mm
Swivel interference	182 mm

FITTING

Fitting type	Bolt hole
Bolt hole diameter	13 mm

CORE ATTRIBUTES

Product name	Alpha stainless
Type	Swivel castor
Load capacity at 3 km/h	80 kg
Load capacity at 4 km/h	80 kg
Load capacity at 6 km/h	80 kg
Stainless	✓
Load capacity Static	160 kg
Overall height	128 mm
Overall weight	0 kg

WHEEL

Body material	Aluminium
Tread material	Damping, heat resistant
Bearing	Precision ball bearing, stainless
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	100 mm
Tread width	35 mm