

PRODUCT INFORMATION

ELASTECH

IEP 100x40 HL49 asm.

EAN 4031582319675



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Elastech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	440.92 lb
Electric conductive	no
Stainless	no
Load capacity Static	881.85 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	185 °F
Overall weight	1.14 lb

WHEEL

Tread hardness	soft
Body material	Aluminum
Tread material	Elastic tire, black, vulcanized
Bearing	Precision ball bearing
Wheel color	Metallic
Threadguards	Without threadguard
Diameter	3.94 in
Tread width	1.57 in
Axle hole diameter	0.31 in
Hub length	1.93 in
Body width	1.57 in
Hardness of tread (A)	68 Shore A

ELASTECH

IEP 100x40 HL49 asm.


EAN 4031582319675

Order number 00043125

Product Drawings



BETTER MOBILITY. BETTER LIFE.




PRODUCT INFORMATION

ELASTECH

IEP 100x40 HL49 asm.

EAN 4031582319675

Order number 001425



BETTER MOBILITY. BETTER LIFE.