

AGILA STAINLESS

7470PJO100P30-13

EAN 4031582350166
Order number 00036322



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ● ● |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ● ● |

CORE ATTRIBUTES

| | |
|-----------------------------|---------------------------|
| Product name | Agila stainless |
| Type | Swivel castor |
| Standard | EN12530 - Devices Castors |
| Load capacity at 3 km/h | 80 kg |
| Stainless | ✓ |
| Load capacity Static | 160 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 60 °C |
| Overall height | 135 mm |
| Overall width | 60 mm |
| Overall weight | 0.503 kg |

WHEEL

| | |
|-----------------------|-----------------------|
| Body material | Polypropylene |
| Tread material | Thermoplastic rubber |
| Bearing | Plain bearing |
| Wheel color | Silver grey (RAL7001) |
| Threadguards | Without threadguard |
| Diameter | 100 mm |
| Tread width | 32 mm |
| Body width | 32 mm |
| Hardness of tread (A) | 87 Shore A |

HOUSING

| | |
|---------------------|-------------------------|
| Material fork | Stainless steel, medium |
| Fork shape | Broad |
| Swivel bearing | Two ball races |
| Colour | Stainless steel |
| Offset | 38 mm |
| Swivel radius | 88 mm |
| Swivel interference | 176 mm |
| Dome diameter | 60 mm |

FITTING

| | |
|--------------------|--|
| Fitting type | Bolt hole |
| Bolt hole diameter | 13 mm |
| Hint | Castors can be mounted with standard screws of any length. |

AGILA STAINLESS

7470PJO100P30-13

EAN 4031582350166
Order number 00036322



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

