

NOVATECH

FTP 250X60-Ø30 HL60

EAN 4031582319408

Broj porudžbine 00801341



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	Ливено Гвожђе
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj
Boja Tocak	Med žuta (RAL1005)
stitnici omotaca	Sa threadguard
Prečnik	250 mm
Širina omotac	60 mm
dimenzija rupa osovina	30 mm
dužina glavcine	60 mm
Širina tela	60 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D

PERFORMANSE

Performanse kotrljanja ●●●●○

Buka u pokretu ●●●○○

Ishrana ●●●●○

otpornost na rdju ●●●○○

OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Tip	Tocak
Standard	EN12533 - Tockoviza teske terete
Nosivost na 4 km/h	1680 kg
Nosivost na 6 km/h	1400 kg
Statički Nosivost	2800 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	7,064 kg

NOVATECH

FTP 250X60-Ø30 HL60

EAN 4031582319408
Broj porudžbine 00801341



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

