

# ALPHA STAINLESS

8470IDC100P30-13 TDK

EAN 4031582382174



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## CORE ATTRIBUTES

|                          |                 |
|--------------------------|-----------------|
| Product name             | Alpha stainless |
| Type                     | Swivel caster   |
| Load capacity at 1.8 mph | 176.37 lb       |
| Load capacity at 2.5 mph | 176.37 lb       |
| Load capacity at 3.7 mph | 176.37 lb       |
| Electric conductive      | no              |
| Stainless                | Yes             |
| Load capacity Static     | 352.74 lb       |
| Overall height           | 5.04 in         |
| Overall weight           | 0 lb            |

## HOUSING

|                     |                        |
|---------------------|------------------------|
| Housing Material    | Stainless steel, heavy |
| Fork shape          | Broad                  |
| Swivel bearing      | Two ball races         |
| Housing Color       | Stainless steel        |
| Offset              | 1.61 in                |
| Swivel radius       | 3.58 in                |
| Swivel interference | 7.17 in                |

## WHEEL

|                |                                   |
|----------------|-----------------------------------|
| Body material  | Aluminum                          |
| Tread material | Damping, heat resistant           |
| Bearing        | Precision ball bearing, stainless |
| Axle           | Screwed with nut                  |
| Threadguards   | Without threadguard               |
| Diameter       | 3.94 in                           |
| Tread width    | 1.38 in                           |

## FITTING

|                    |           |
|--------------------|-----------|
| Fitting type       | Bolt hole |
| Bolt hole diameter | 0.51 in   |