

GALEA STAINLESS

5080PJC100P30-12

EAN 4031582395747



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja ●●●●○

Buka u pokretu ●●●●○

Ishrana ●●●●○

otpornost na rdju ●●●○

OSNOVNI ATRIBUTI

Naziv proizvoda	Galea stainless
Tip	Okretanje Tocak
Standard	EN12530 - Kastori uređaja
Nosivost na 3 km/h	100 kg
nerdjajuci	✓
Statički Nosivost	200 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Sveukupna visina	139 mm
Ukupna širina	66 mm
Ukupna težina	0,434 kg

TOCAK

Materijal za telo	polipropilen
materijal omotaca	Termoplastična guma
Nošenje	precizini kuglicni lezaj, nerdjajuci
stitnici omotaca	Sa threadguard
Prečnik	100 mm
Širina omotac	30 mm
Teškoća gazećeg omotac (A)	87 Šora A

KUCISTE

Materijal	poliamid
oblik viljuska	Zatvoreno
okretni lezaj	Dve trke za loptu, Ojacano ili nerdjajuci
ofset	40 mm
okretni radijus	90 mm
Otpor okretanju	180 mm
Prečnik kupole	59 mm

PRILAGOĐAVANJE

Tip uklapanja	otvor za vijak
dimenzija rupa sraf	12 mm

GALEA STAINLESS

5080PJC100P30-12

EAN 4031582395747



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

