

# STYLEA

5920UOI035L51-10 LH 9011/9011

EAN 4031582356731



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ○ ○ |
| Movement Noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ● |
| Corrosion Resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                             |
|-----------------------------|-----------------------------|
| Product Name                | Stylea                      |
| Type                        | Swivel castor               |
| Standard                    | EN12528 - Furniture Castors |
| Load capacity at 3 km/h     | 50 kg                       |
| Electric Conductive         | No                          |
| Stainless                   | No                          |
| Load capacity Static        | 100 kg                      |
| Temperature range (Minimum) | -20 °C                      |
| Temperature range (Maximum) | 60 °C                       |
| Overall Height              | 33 mm                       |
| Overall width               | 52 mm                       |
| Overall weight              | 0.05 kg                     |

## HOUSING

|                     |                          |
|---------------------|--------------------------|
| Housing Material    | Polyamide                |
| Fork shape          | Twin wheel housing       |
| Swivel Bearing      | Stem, swiveling          |
| Housing Color       | Graphite black (RAL9011) |
| Offset              | 12 mm                    |
| Swivel radius       | 37 mm                    |
| Swivel interference | 74 mm                    |
| Dome diameter       | 15.2 mm                  |

## WHEEL

|                    |                                |
|--------------------|--------------------------------|
| Body material      | Polyamide                      |
| Tread Material Mix | Identical with wheel body      |
| Bearing            | Plain bearing with spacer tube |
| Axle               | Riveted                        |
| Threadguards       | Without threadguard            |
| Diameter           | 35 mm                          |
| Tread width        | 12 mm                          |
| Body width         | 12 mm                          |

## FITTING

|                    |                    |
|--------------------|--------------------|
| Fitting type       | Blind hole for B10 |
| Bolt hole diameter | 10 mm              |

# STYLEA

5920UOI035L51-10 LH 9011/9011

EAN 4031582356731

Order number 00078712

Product Drawings



BETTER MOBILITY. BETTER LIFE.

