

ZETA

4681ITP125P63 FlatXL

EAN 4031582400427



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ○ |
| Movement Noise       | ● ● ● ● ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion Resistance | ● ● ● ● ○ |

CORE ATTRIBUTES

|                             |                                     |
|-----------------------------|-------------------------------------|
| Product Name                | Zeta                                |
| Type                        | Swivel castor with directional lock |
| Standard                    | EN12532 - Transport Equipment       |
| Load capacity at 4 km/h     | 500 kg                              |
| Load capacity at 6 km/h     | 400 kg                              |
| Electric Conductive         | No                                  |
| Stainless                   | No                                  |
| Load capacity Static        | 1000 kg                             |
| Temperature range (Minimum) | -0.33 °C                            |
| Overall Height              | 164 mm                              |
| Overall weight              | 2.86 kg                             |

HOUSING

|                     |                                         |
|---------------------|-----------------------------------------|
| Housing Material    | Steel sheet, very heavy                 |
| Fork shape          | Broad, reinforced                       |
| Swivel Bearing      | Two ball races, reinforced or stainless |
| Housing Color       | Blue passivated                         |
| Offset              | 55 mm                                   |
| Swivel interference | 230 mm                                  |

WHEEL

|                       |                        |
|-----------------------|------------------------|
| Tread profile         | flat                   |
| Body material         | Aluminium              |
| Tread Material Mix    | PUR casted premium     |
| Bearing               | Precision ball bearing |
| Axle                  | Screwed with nut       |
| Threadguards          | Without threadguard    |
| Diameter              | 125 mm                 |
| Tread width           | 50 mm                  |
| Hardness of tread (A) | 92 Shore A             |

FITTING

|                             |                          |
|-----------------------------|--------------------------|
| Fitting type                | Medium rectangular plate |
| Plate length                | 137 mm                   |
| Plate width                 | 105 mm                   |
| Plate hole length (Maximum) | 105 mm                   |
| Plate hole width (Minimum)  | 75 mm                    |
| Plate hole width (Maximum)  | 80 mm                    |
| Plate hole diameter         | 11 mm                    |

# ZETA

4681ITP125P63 FlatXL

EAN 4031582400427



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

