

FOOTMASTER

FOOT MASTER GASD-150-ASF-HUD

EAN 4031582495225



BETTER MOBILITY. BETTER LIFE.




Image may differ from the original product

PERFORMANCE

Roll Performance	○ ○ ○ ○ ○
Movement Noise	○ ○ ○ ○ ○
Attrition	○ ○ ○ ○ ○
Corrosion Resistance	○ ○ ○ ○ ○

CORE ATTRIBUTES

Product Name	Footmaster
Type	Swivel castor
Load capacity at 3 km/h	630 kg
Electric Conductive	No
Stainless	No
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	90 °C
Overall Height	200 mm
Overall width	160 mm
Overall weight	17.54 kg

HOUSING

Offset	37 mm
Swivel radius	122 mm
Swivel interference	244 mm
Dome diameter	145 mm

WHEEL

Bearing	Unmachined hub
Diameter	150 mm
Tread width	40 mm
Body width	40 mm

FITTING

Plate length	145 mm
Plate width	145 mm
Plate hole length (Maximum)	120 mm
Plate hole width (Maximum)	120 mm
Plate hole diameter	11 mm

FOOTMASTER

FOOT MASTER GASD-150-ASF-HUD

EAN 4031582495225

Order number 00800107
Product Drawings



BETTER MOBILITY. BETTER LIFE.

