

FOOTMASTER

FOOT MASTER GAGD-125-ASF-HUD

EAN 4031582495294



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	○ ○ ○ ○ ○
Movement Noise	○ ○ ○ ○ ○
Attrition	○ ○ ○ ○ ○
Corrosion Resistance	○ ○ ○ ○ ○

CORE ATTRIBUTES

Product Name	Footmaster
Type	Swivel castor
Load capacity at 3 km/h	440 kg
Electric Conductive	No
Stainless	No
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	90 °C
Overall Height	175 mm
Overall width	128 mm
Overall weight	10.68 kg

HOUSING

Offset	33 mm
Swivel radius	100 mm
Swivel interference	200 mm
Dome diameter	130 mm

WHEEL

Bearing	Unmachined hub
Diameter	125 mm
Tread width	35 mm
Body width	35 mm

FITTING

Plate length	145 mm
Plate width	145 mm
Plate hole length (Maximum)	120 mm
Plate hole width (Maximum)	120 mm
Plate hole diameter	11 mm

FOOTMASTER

FOOT MASTER GAGD-125-ASF-HUD

EAN 4031582495294

Order number 00800104
Product Drawings



BETTER MOBILITY. BETTER LIFE.

