

# FORMA

6941UFP125P33 WHITE

EAN 4031582477375



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ● ○ |
| Movement noise       | ● ● ● ● ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                                     |
|-----------------------------|-------------------------------------|
| Product name                | Forma                               |
| Type                        | Swivel castor with directional lock |
| Load capacity at 3 km/h     | 125 kg                              |
| Temperature range (Minimum) | -18 °C                              |
| Temperature range (Maximum) | 120 °C                              |
| Overall height              | 166 mm                              |

## WHEEL

|                       |                                       |
|-----------------------|---------------------------------------|
| Body material         | Polyamide                             |
| Tread hardness        | soft                                  |
| Tread material        | Elastic tire, non-marking, vulcanized |
| Bearing               | Precision ball bearing                |
| Threadguards          | With threadguard                      |
| Diameter              | 125 mm                                |
| Tread width           | 18 mm                                 |
| Hardness of tread (A) | 60 Shore A                            |

## HOUSING

|                |                              |
|----------------|------------------------------|
| Material fork  | Zinc-die-casting / Aluminium |
| Fork shape     | Twin wheel housing           |
| Swivel bearing | Precision ball bearing       |
| Offset         | 41 mm                        |
| Swivel radius  | 117 mm                       |

## FITTING

|                             |                   |
|-----------------------------|-------------------|
| Fitting type                | Rectangular plate |
| Plate length                | 92 mm             |
| Plate width                 | 64 mm             |
| Plate hole length (Maximum) | 73 mm             |
| Plate hole width (Minimum)  | 43 mm             |
| Plate hole width (Maximum)  | 45 mm             |
| Plate hole diameter         | 10.7 mm           |

# FORMA

6941UFP125P33 WHITE

EAN 4031582477375



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

