

# LINEA CLINIC

5946UAP150R36-34XS S30 D 9002

EAN 4031582348378



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ● |
| Movement Noise       | ● ● ● ● ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion Resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                                        |
|-----------------------------|----------------------------------------|
| Product Name                | Linea clinic                           |
| Type                        | Swivel castor with central, total lock |
| Standard                    | EN12531 - Hospital Bed Castors         |
| Load capacity at 3 km/h     | 150 kg                                 |
| Load capacity at 4 km/h     | 150 kg                                 |
| Electric Conductive         | No                                     |
| Stainless                   | No                                     |
| Load capacity Static        | 450 kg                                 |
| Temperature range (Minimum) | -10 °C                                 |
| Temperature range (Maximum) | 40 °C                                  |
| Overall Height              | 155 mm                                 |
| Overall width               | 71 mm                                  |
| Overall weight              | 1.03 kg                                |
| Certification               | Tested and monitored by TÜV Süd        |

## HOUSING

|                     |                        |
|---------------------|------------------------|
| Housing Material    | Polyamide              |
| Fork shape          | Twin wheel housing     |
| Swivel Bearing      | Precision ball bearing |
| Housing Color       | Grey white (RAL9002)   |
| Offset              | 47.5 mm                |
| Swivel radius       | 127 mm                 |
| Swivel interference | 254 mm                 |
| Dome diameter       | 45.5 mm                |

## WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Polyamide              |
| Tread Material Mix    | Polyurethane, injected |
| Bearing               | Precision ball bearing |
| Wheel Color           | Grey white (RAL9002)   |
| Threadguards          | With threadguard       |
| Diameter              | 150 mm                 |
| Tread width           | 15 mm                  |
| Body width            | 15 mm                  |
| Hardness of tread (A) | 92 Shore A             |
| Hardness of tread (D) | 42 Shore D             |

## FITTING

|               |                                                    |
|---------------|----------------------------------------------------|
| Fitting type  | Stem with cam hole for profile bars, short version |
| Bolt diameter | 32 mm                                              |
| Bolt length   | 42 mm                                              |

Deutscher  
Designer  
ClubIF Design  
AwardInterzum  
Award

# LINEA CLINIC

5946UAP150R36-34XS S30 D 9002



EAN 4031582348378

Order number 00034521

Product Drawings



BETTER MOBILITY. BETTER LIFE.



Deutscher  
Designer  
Club



IF Design  
Award



Interzum  
Award

product  
design  
award