

# LEVINA LIGHT

5225PJP075L51-10 9011

EAN 4031582496659



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ○ |
| Movement noise       | ● ● ● ● ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                                |
|-----------------------------|--------------------------------|
| Product name                | Levina light                   |
| Type                        | Swivel caster with wheel brake |
| Standard                    | EN12530 - Devices Castors      |
| Load capacity at 1.8 mph    | 165.35 lb                      |
| Electric conductive         | no                             |
| Stainless                   | no                             |
| Load capacity Static        | 330.69 lb                      |
| Temperature range (Minimum) | 14 °F                          |
| Temperature range (Maximum) | 104 °F                         |
| Overall height              | 4.06 in                        |
| Overall weight              | 0.39 lb                        |

## HOUSING

|                     |                          |
|---------------------|--------------------------|
| Housing Material    | Polyamide                |
| Fork shape          | Straight                 |
| Swivel bearing      | Stem, swiveling          |
| Housing Color       | Graphite black (RAL9011) |
| Offset              | 1.06 in                  |
| Swivel radius       | 2.87 in                  |
| Swivel interference | 5.75 in                  |

## WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Polypropylene          |
| Tread material        | Thermoplastic rubber   |
| Bearing               | Precision ball bearing |
| Threadguards          | With threadguard       |
| Diameter              | 2.95 in                |
| Tread width           | 0.98 in                |
| Hardness of tread (A) | 87 Shore A             |

## FITTING

|                    |                            |
|--------------------|----------------------------|
| Fitting type       | Blind hole for B10 fitting |
| Bolt hole diameter | 0.39 in                    |

# LEVINA LIGHT

5225PJP075L51-10 9011

EAN 4031582496659

Order number 00038792LV  
Product Drawings



BETTER MOBILITY. BETTER LIFE.

