

# GALEA

5070PJH125P30-12

EAN 4031582378641



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ○ |
| Movement noise       | ● ● ● ● ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                           |
|-----------------------------|---------------------------|
| Product name                | Galea                     |
| Type                        | Swivel caster             |
| Standard                    | EN12530 - Devices Castors |
| Load capacity at 1.8 mph    | 220.46 lb                 |
| Electric conductive         | no                        |
| Stainless                   | no                        |
| Load capacity Static        | 440.92 lb                 |
| Temperature range (Minimum) | -4 °F                     |
| Temperature range (Maximum) | 140 °F                    |
| Overall height              | 6.38 in                   |
| Overall width               | 2.6 in                    |
| Overall weight              | 1.11 lb                   |

## HOUSING

|                     |                |
|---------------------|----------------|
| Housing Material    | Polyamide      |
| Fork shape          | Closed         |
| Swivel bearing      | Two ball races |
| Offset              | 1.57 in        |
| Swivel radius       | 4.04 in        |
| Swivel interference | 8.07 in        |
| Dome diameter       | 2.32 in        |

## WHEEL

|                       |                      |
|-----------------------|----------------------|
| Body material         | Polypropylene        |
| Tread material        | Thermoplastic rubber |
| Bearing               | Plain bearing        |
| Threadguards          | With threadguard     |
| Diameter              | 4.92 in              |
| Tread width           | 1.18 in              |
| Hardness of tread (A) | 87 Shore A           |

## FITTING

|                    |           |
|--------------------|-----------|
| Fitting type       | Bolt hole |
| Bolt hole diameter | 0.47 in   |

# GALEA

5070PJH125P30-12

EAN 4031582378641

Order number 00770899  
Product Drawings



BETTER MOBILITY. BETTER LIFE.

