

FOOTMASTER

FOOT MASTER GD-100-S-NYN

EAN 4031582413250



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja	○ ○ ○ ○ ○
Buka u pokretu	○ ○ ○ ○ ○
Ishrana	○ ○ ○ ○ ○
otpornost na rdju	○ ○ ○ ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Footmaster
Tip	Okretanje Tocak
Nosivost na 3 km/h	800 kg
Električni provod	no
nerdjajuci	no
Statički Nosivost	800 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	90 °C
Sveukupna visina	120 mm
Ukupna širina	98 mm
Ukupna težina	1.4 kg

KUCISTE

Boja	Beli
ofset	53 mm
okretni radijus	90.5 mm
Otpor okretanju	181 mm
Prečnik kupole	98 mm

TOCAK

Nošenje	kotrljajuci lezaj, navlažen
Boja Tocak	Crna
Prečnik	75 mm
Širina omotac	30 mm
Širina tela	30 mm

FOOTMASTER

FOOT MASTER GD-100-S-NYN

EAN 4031582413250

Broj porudžbine 00062071
Crteži proizvoda



BETTER MOBILITY. BETTER LIFE.

