

# EXPANDER

R07-Ø36-39

EAN 4031582438284



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## FITTING

|                            |                                                            |
|----------------------------|------------------------------------------------------------|
| Fitting type               | Synthetic expander, round                                  |
| Expander fitting (Minimum) | 1.42 in                                                    |
| Expander fitting (Maximum) | 1.57 in                                                    |
| Hint                       | Please indicate required tube innerdiameter when ordering. |

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Corrosion resistance | ● ● ● ○ ○ |
|----------------------|-----------|

## CORE ATTRIBUTES

|                             |           |
|-----------------------------|-----------|
| Product name                | Expander  |
| Type                        | Accessory |
| Electric conductive         | no        |
| Stainless                   | Yes       |
| Temperature range (Minimum) | 14 °F     |
| Temperature range (Maximum) | 104 °F    |
| Overall weight              | 0.39 lb   |