

# OMIKRON TWIN

9958FTP150P65

EAN 4031582316940



BETTER MOBILITY. BETTER LIFE.




Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ○ |
| Movement Noise       | ● ● ● ● ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion Resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                                       |
|-----------------------------|---------------------------------------|
| Product Name                | Omikron twin                          |
| Type                        | Fixed castor                          |
| Standard                    | similar EN12532 - Transport Equipment |
| Load capacity at 4 km/h     | 1800 kg                               |
| Load capacity at 6 km/h     | 1400 kg                               |
| Electric Conductive         | No                                    |
| Stainless                   | No                                    |
| Load capacity Static        | 3600 kg                               |
| Temperature range (Minimum) | -10 °C                                |
| Temperature range (Maximum) | 60 °C                                 |
| Overall Height              | 245 mm                                |
| Overall width               | 189 mm                                |
| Overall weight              | 11.99 kg                              |

## HOUSING

|                    |                     |
|--------------------|---------------------|
| Housing Material   | Iron forged, heavy  |
| Fork shape         | Twin wheel housing  |
| Housing Color      | Transparent coating |
| Lubrication nipple | 1                   |
| Dome diameter      | 160 mm              |

## WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Cast iron              |
| Tread Material Mix    | PUR casted premium     |
| Bearing               | Precision ball bearing |
| Axle                  | Screwed with nut       |
| Wheel Color           | Honey yellow (RAL1005) |
| Threadguards          | With threadguard       |
| Diameter              | 150 mm                 |
| Tread width           | 50 mm                  |
| Body width            | 50 mm                  |
| Hardness of tread (A) | 92 Shore A             |
| Hardness of tread (D) | 42 Shore D             |

## FITTING

|                             |                                     |
|-----------------------------|-------------------------------------|
| Fitting type                | Medium rectangular heavy-duty plate |
| Plate length                | 200 mm                              |
| Plate width                 | 160 mm                              |
| Plate hole length (Maximum) | 120 mm                              |
| Plate hole width (Maximum)  | 160 mm                              |
| Plate hole diameter         | 15 mm                               |

# OMIKRON TWIN

9958FTP150P65

EAN 4031582316940

Order number 00806805

Product Drawings



BETTER MOBILITY. BETTER LIFE.

