

# MAXTECH

PAP125x30-Ø8

EAN 4031582387513



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ○ ○ |
| Movement Noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion Resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                           |
|-----------------------------|---------------------------|
| Product Name                | Maxtech                   |
| Type                        | Wheel                     |
| Standard                    | EN12530 - Devices Castors |
| Load capacity at 3 km/h     | 150 kg                    |
| Electric Conductive         | No                        |
| Stainless                   | No                        |
| Load capacity Static        | 300 kg                    |
| Temperature range (Minimum) | -20 °C                    |
| Temperature range (Maximum) | 60 °C                     |

## WHEEL

|                    |                        |
|--------------------|------------------------|
| Body material      | Polypropylene          |
| Tread Material Mix | Polyurethane, injected |
| Bearing            | Precision ball bearing |
| Threadguards       | With threadguard       |
| Diameter           | 125 mm                 |
| Tread width        | 30 mm                  |
| Axle Hole Diameter | 8 mm                   |

