

# LEVINA STAINLESS

5387UAC150P30-13

EAN 4031582364460



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |             |
|----------------------|-------------|
| Roll Performance     | ● ● ● ● ○ ○ |
| Movement noise       | ● ● ● ● ○   |
| Attrition            | ● ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ● ● ● |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Levina stainless              |
| Type                        | Swivel caster with total lock |
| Standard                    | EN12530 - Devices Castors     |
| Load capacity at 1.8 mph    | 220.46 lb                     |
| Electric conductive         | no                            |
| Stainless                   | Yes                           |
| Load capacity Static        | 440.92 lb                     |
| Temperature range (Minimum) | 14 °F                         |
| Temperature range (Maximum) | 104 °F                        |
| Overall height              | 7.48 in                       |

## HOUSING

|                     |                                         |
|---------------------|-----------------------------------------|
| Housing Material    | Polyamide                               |
| Fork shape          | Slim                                    |
| Swivel bearing      | Two ball races, reinforced or stainless |
| Offset              | 1.5 in                                  |
| Swivel interference | 9.45 in                                 |

## WHEEL

|                       |                                   |
|-----------------------|-----------------------------------|
| Body material         | Polyamide                         |
| Tread material        | Polyurethane, injected            |
| Bearing               | Precision ball bearing, stainless |
| Threadguards          | With threadguard                  |
| Diameter              | 5.91 in                           |
| Tread width           | 1.26 in                           |
| Hardness of tread (A) | 92 Shore A                        |
| Hardness of tread (D) | 40 Shore D                        |

## FITTING

|                    |           |
|--------------------|-----------|
| Fitting type       | Bolt hole |
| Bolt hole diameter | 0.51 in   |



Universal  
Design  
Award



Deutscher  
Designer  
Club

# LEVINA STAINLESS

5387UAC150P30-13

EAN 4031582364460



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

---

