PRODUCT INFORMATION

ELASTECH

IEP 250x50-Ø25 HL60

EAN 4031582319767

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Tread hardness	soft
Body material	Aluminum
Tread material	Elastic tire, black, vulcanized
Bearing	Precision ball bearing
Wheel color	Jet black (similar RAL9005)
Threadguards	Without threadguard
Diameter	9.84 in
Tread width	1.97 in
Axle hole diameter	0.98 in
Hub length	2.36 in
Body width	1.97 in
Hardness of tread (A)	68 Shore A

PERFORMANCE

Roll Performance	●●○○○
Movement noise	●●●●●
Attrition	●●●○○
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Elastech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	1102.31 lb
Load capacity at 3.7 mph	881.85 lb
Electric conductive	no
Stainless	no
Load capacity Static	2204.62 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	185 °F
Overall weight	5.16 lb

© Copyright 2026 TENTE International GmbH


ELASTECH

IEP 250x50-Ø25 HL60

EAN 4031582319767

Order number 00801257

Product Drawings




© Copyright 2026 TENTE International GmbH

ELASTECH

IEP 250x50-Ø25 HL60

EAN 4031582319767

Order number 00301257



BETTER MOBILITY. BETTER LIFE.

© Copyright 2026 TENTE International GmbH