PRODUCT INFORMATION

# NOVATECH

## ETX082x70-Ø17 HL75-B

EAN 4031582331936



Image may differ from the original product

### WHEEL

| | |
|---|---|
| Body material | Steel, iron |
| Tread Material Mix | PUR casted premium |
| Bearing | Precision ball bearing, sealed |
| Threadguards | With threadguard |
| Diameter | 82 mm |
| Tread width | 70 mm |
| Axle Hole Diameter | 17 mm |
| Hub Length | 75 mm |
| Hardness of tread (A) | 92 Shore A |
| Bearing type | 6303 |
| Sealing type | B |
| Suitable for | jungheinrich_mic |

### PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●○○ |
| Movement Noise | ●●●○○ |
| Attrition | ●●●●○ |
| Corrosion Resistance | ●●●○○ |

### CORE ATTRIBUTES

| | |
|---|---|
| Product Name | Novatech |
| Type | Wheel |
| Load capacity at 3 km/h | 700 kg |
| Electric Conductive | No |
| Stainless | No |
| Load capacity Static | 1400 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 60 °C |
| Overall weight | 1 kg |

© Copyright 2026 TENTE International GmbH

# NOVATECH

ETX082x70-Ø17 HL75-B

EAN 4031582331936

BETTER MOBILITY. BETTER LIFE.

## Product Drawings







