

# ZETA STAINLESS

8671UAD200P63

EAN 4031582313611  
Order number 00830139



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ● ● |
| Movement noise       | ● ● ○ ○ ○ |
| Attrition            | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ● ● |

## CORE ATTRIBUTES

|                             |                                     |
|-----------------------------|-------------------------------------|
| Product name                | Zeta stainless                      |
| Type                        | Swivel castor with directional lock |
| Standard                    | EN12533 - Heavy Duty Castors        |
| Load capacity at 4 km/h     | 500 kg                              |
| Load capacity at 6 km/h     | 400 kg                              |
| Stainless                   | ✓                                   |
| Load capacity Static        | 1000 kg                             |
| Temperature range (Minimum) | -30 °C                              |
| Temperature range (Maximum) | 80 °C                               |
| Overall height              | 240 mm                              |
| Overall width               | 96 mm                               |
| Overall weight              | 3.294 kg                            |

## WHEEL

|                       |                           |
|-----------------------|---------------------------|
| Body material         | Polyamide                 |
| Tread material        | Polyurethane, injected    |
| Bearing               | Roller bearing, stainless |
| Axle                  | Screwed with nut          |
| Wheel color           | Natural white             |
| Diameter              | 200 mm                    |
| Tread width           | 50 mm                     |
| Body width            | 50 mm                     |
| Hardness of tread (A) | 92 Shore A                |
| Hardness of tread (D) | 42 Shore D                |

## HOUSING

|                     |                        |
|---------------------|------------------------|
| Material fork       | Stainless steel, heavy |
| Fork shape          | Broad, reinforced      |
| Swivel bearing      | Two ball races         |
| Colour              | Stainless steel        |
| Offset              | 55 mm                  |
| Swivel radius       | 155 mm                 |
| Swivel interference | 310 mm                 |
| Dome diameter       | 96 mm                  |

## FITTING

|                             |                          |
|-----------------------------|--------------------------|
| Fitting type                | Medium rectangular plate |
| Plate length                | 137 mm                   |
| Plate width                 | 105 mm                   |
| Plate hole length (Minimum) | 74 mm                    |
| Plate hole length (Maximum) | 80 mm                    |
| Plate hole width (Minimum)  | 74 mm                    |
| Plate hole width (Maximum)  | 105 mm                   |
| Plate hole diameter         | 11 mm                    |

# ZETA STAINLESS

8671UAD200P63

EAN 4031582313611  
Order number 00830139



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

