PRODUCT INFORMATION

E-DRIVE OPTIMA

EDOAUFF125P60 24V fuer optima

BETTER MOBILITY. BETTER LIFE.

PERFORMANCE

Roll Performance	●●●●○
Movement Noise	●●●●○
Attrition	●●●○○
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	E-Drive optima
Type	Drive Unit
Electric Conductive	No
Stainless	No
Temperature range (Minimum)	5 °C
Temperature range (Maximum)	40 °C
Overall width	190 mm
Overall weight	3.99 kg

HOUSING

Housing Material	Electric
Fork shape	Drive
Swivel Bearing	O-E-Drive optima
Housing Color	Blue passivated

WHEEL

Body material	Polyamide
Tread Material Mix	Elastic tire, non-marking, vulcanized
Bearing	Flanged wheel
Wheel Color	Silver grey (RAL7001)
Diameter	125 mm
Body width	40 mm
Hardness of tread (A)	63 Shore A

FITTING

Fitting type	Rectangular plate
Plate length	100 mm
Plate width	95 mm
Plate hole length (Maximum)	60 mm
Plate hole width (Maximum)	100 mm
Plate hole diameter	9 mm

© Copyright 2026 TENTE International GmbH