PRODUCT INFORMATION

LUMINA

5520UOI075L51-11 RAL9006

EAN 4031582310658



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●○○
Attrition	●●●●●
Corrosion Resistance	●●●●○

CORE ATTRIBUTES

Product Name	Lumina
Type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	100 kg
Electric Conductive	No
Stainless	No
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall Height	88 mm
Overall width	65 mm
Overall weight	0.28 kg

HOUSING

Housing Material	Polyamide
Fork shape	Twin wheel housing, closed, with dome
Swivel Bearing	Stem, swiveling
Housing Color	White aluminium (RAL9006)
Offset	30 mm
Swivel radius	73 mm
Swivel interference	146 mm
Dome diameter	45 mm

WHEEL

Body material	Polyamide
Tread Material Mix	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	75 mm
Tread width	10 mm
Hardness of tread (D)	75 Shore D

FITTING

Fitting type	Blind hole for B10
Bolt hole diameter	11 mm

© Copyright 2026 TENTE International GmbH


LUMINA

5520UOI075L51-11 RAL9006

EAN 4031582310658

Order number 00073439

Product Drawings



© Copyright 2026 TENTE International GmbH