PRODUCT INFORMATION

# LINEA LIGHT

## 5925PJI040P41-38x38/10 LOW SET

EAN 4031582440560

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

### PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●○○ |
| Movement Noise | ●●●○○ |
| Attrition | ●●●●● |
| Corrosion Resistance | ●●●●○ |

### CORE ATTRIBUTES

| | |
|---|---|
| Product Name | Linea light |
| Type | Swivel castor with wheel brake |
| Standard | EN12528 - Furniture Castors |
| Load capacity at 3 km/h | 40 kg |
| Electric Conductive | No |
| Stainless | No |
| Load capacity Static | 80 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 60 °C |
| Overall Height | 43.5 mm |
| Overall width | 52 mm |
| Overall weight | 0.05 kg |

### HOUSING

| | |
|---|---|
| Housing Material | Polyamide |
| Fork shape | Twin wheel housing |
| Swivel Bearing | Stem, swiveling |
| Offset | 12 mm |
| Swivel radius | 45 mm |
| Swivel interference | 90 mm |

### WHEEL

| | |
|---|---|
| Body material | Polypropylene |
| Tread Material Mix | Thermoplastic rubber |
| Bearing | Plain bearing with spacer tube |
| Threadguards | Without threadguard |
| Diameter | 40 mm |
| Tread width | 12 mm |
| Hardness of tread (A) | 87 Shore A |

### FITTING

| | |
|---|---|
| Fitting type | Square plate |
| Plate length | 38 mm |
| Plate width | 38 mm |
| Plate hole length (Maximum) | 27 mm |
| Plate hole width (Maximum) | 27 mm |
| Plate hole diameter | 5 mm |

Deutscher Designer Club

Interzum Award

IF Design Award

© Copyright 2026 TENTE International GmbH