PRODUCT INFORMATION

# DURATECH HEAT

## BOG080x35-Ø12

EAN 4031582436730



Image may differ from the original product

### PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●○○ |
| Movement Noise | ●●●○○ |
| Attrition | ●●●●● |
| Corrosion Resistance | ●●●●● |

### CORE ATTRIBUTES

| | |
|---|---|
| Product Name | Duratech heat |
| Type | Wheel |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 100 kg |
| Electric Conductive | No |
| Stainless | No |
| Load capacity Static | 200 kg |
| Temperature range (Minimum) | -40 °C |
| Temperature range (Maximum) | 280 °C |
| Overall weight | 0.18 kg |

### WHEEL

| | |
|---|---|
| Body material | Plastic thermoset, heat-resistant |
| Tread Material Mix | Identical with wheel body |
| Bearing | Dry bearing bush |
| Diameter | 80 mm |
| Tread width | 35 mm |
| Axle Hole Diameter | 12 mm |
| Hub Length | 43.5 mm |
| Hardness of tread (D) | 85 Shore D |

© Copyright 2026 TENTE International GmbH