PRODUCT INFORMATION

# AGILA

2478DYK075P60-67X60

EAN 4031582344523

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●○○ |
| Movement Noise | ●●●●○ |
| Attrition | ●●●○○ |
| Corrosion Resistance | ●●●○○ |

## CORE ATTRIBUTES

| | |
|---|---|
| Product Name | Agila |
| Type | Fixed castor |
| Standard | EN12530 - Devices Castors |
| Load capacity at 3 km/h | 55 kg |
| Electric Conductive | Yes |
| Stainless | No |
| Load capacity Static | 110 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 60 °C |
| Overall Height | 100 mm |
| Overall width | 43 mm |
| Overall weight | 0.29 kg |

## HOUSING

| | |
|---|---|
| Housing Material | Steel sheet, medium |
| Fork shape | Broad |
| Housing Color | Blue passivated |
| Dome diameter | 43 mm |

## WHEEL

| | |
|---|---|
| Body material | Sheet Steel |
| Tread Material Mix | Solid rubber, black, electric-conductive |
| Bearing | Cone ball bearing |
| Wheel Color | Blue passivated |
| Threadguards | With threadguard |
| Diameter | 75 mm |
| Tread width | 25 mm |
| Body width | 25 mm |
| Hardness of tread (A) | 80 Shore A |

## FITTING

| | |
|---|---|
| Fitting type | Rectangular plate |
| Plate length | 67 mm |
| Plate width | 60 mm |
| Plate hole length (Minimum) | 40 mm |
| Plate hole length (Maximum) | 48 mm |
| Plate hole width (Minimum) | 40 mm |
| Plate hole width (Maximum) | 48 mm |
| Plate hole diameter | 6.3 mm |

© Copyright 2026 TENTE International GmbH


# AGILA


2478DYK075P60-67X60

EAN 4031582344523

Order number 00028590

**Product Drawings**




© Copyright 2026 TENTE International GmbH