PRODUCT INFORMATION

# STYLEA

## 5925UOI075L51-11 DM20x43ALU

EAN 4031582335989

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

### PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●○○ |
| Movement noise | ●●●○○ |
| Attrition | ●●●●● |
| Corrosion resistance | ●●●●○ |

### CORE ATTRIBUTES

| | |
|---|---|
| Product name | Stylea |
| Type | Swivel caster with wheel brake |
| Standard | EN12528 - Furniture Castors |
| Load capacity at 1.8 mph | 110.23 lb |
| Electric conductive | no |
| Stainless | no |
| Load capacity Static | 220.46 lb |
| Temperature range (Minimum) | 14 °F |
| Temperature range (Maximum) | 104 °F |
| Overall height | 3.48 in |
| Overall width | 2.09 in |

### HOUSING

| | |
|---|---|
| Housing Material | Polyamide |
| Fork shape | Twin wheel housing |
| Swivel bearing | Stem, swiveling |
| Swivel radius | 3.43 in |
| Swivel interference | 6.85 in |
| Dome diameter | 0.79 in |

### WHEEL

| | |
|---|---|
| Body material | Polyamide |
| Tread material | Identical with wheel body |
| Bearing | Plain bearing with spacer tube |
| Axle | Riveted |
| Threadguards | Without threadguard |
| Diameter | 2.95 in |
| Tread width | 0.31 in |

### FITTING

| | |
|---|---|
| Fitting type | Blind hole for B10 fitting |
| Bolt hole diameter | 0.43 in |

© Copyright 2026 TENTE International GmbH


# STYLEA

5925UOI075L51-11 DM20x43ALU

EAN 4031582335989

BETTER MOBILITY. BETTER LIFE.

## Product Drawings



© Copyright 2026 TENTE International GmbH