PRODUCT INFORMATION

STEM

S70-10x15 / 10 drilled stem

EAN 4031582411904

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

FITTING

Fitting type	Threaded stem with hexagon neck, top
Stem diameter	0.39 in
Stem length	0.59 in

PERFORMANCE

Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Stem
Type	Accessory
Load capacity at 1.8 mph	176.37 lb
Electric conductive	no
Stainless	no
Load capacity Static	352.74 lb
Overall height	0.24 in
Overall weight	0.06 lb

© Copyright 2026 TENTE International GmbH