PRODUCT INFORMATION

NOVATECH

FTP 250x80-Ø25 HL92

EAN 4031582319415



Image may differ from the original product

WHEEL

Body material	Cast iron
Tread Material Mix	PUR casted premium
Bearing	Precision ball bearing
Wheel Color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	250 mm
Tread width	80 mm
Axle Hole Diameter	25 mm
Hub Length	92 mm
Body width	80 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

PERFORMANCE

Roll Performance	●●●●○
Movement Noise	●●●○○
Attrition	●●●●○
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Novatech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	2160 kg
Load capacity at 6 km/h	1800 kg
Electric Conductive	No
Stainless	No
Load capacity Static	3600 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall weight	9.22 kg

© Copyright 2026 TENTE International GmbH


NOVATECH

FTP 250x80-Ø25 HL92

EAN 4031582319415

Order number 00800997

Product Drawings




© Copyright 2026 TENTE International GmbH

NOVATECH

FTP 250x80-Ø25 HL92

EAN 4031582319415

Order number 0080097



© Copyright 2026 TENTE International GmbH