PRODUCT INFORMATION

ALPHA

3480PQR260P65 black/darkblue

EAN 4031582438239



Image may differ from the original product

PERFORMANCE

Roll Performance	● ○ ○ ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Alpha
Type	Swivel caster
Load capacity at 1.8 mph	330.69 lb
Electric conductive	no
Stainless	no
Load capacity Static	661.39 lb
Overall height	12.2 in
Overall weight	11.02 lb

HOUSING

Housing Material	Steel sheet, heavy
Fork shape	Broad
Swivel bearing	Two ball races, reinforced or stainless
Housing Color	Blue passivated
Offset	3.54 in
Swivel radius	8.66 in
Swivel interference	17.32 in

WHEEL

Body material	Polypropylene
Tread material	Pneumatic tire, block profile
Bearing	Roller bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	10.24 in
Tread width	3.35 in

FITTING

Fitting type	Rectangular plate
Plate length	7.87 in
Plate width	6.3 in
Plate hole length (Maximum)	6.3 in
Plate hole width (Maximum)	4.72 in
Plate hole diameter	0.55 in

© Copyright 2026 TENTE International GmbH

ALPHA

3480PQR260P65 black/darkblue

EAN 4031582438239

BETTER MOBILITY. BETTER LIFE.

Product Drawings



© Copyright 2026 TENTE International GmbH