PRODUCT INFORMATION

ELASTECH HEAT

IDG100x35-Ø8 (DSG)

EAN 4031582382594

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●○○
Attrition	●●●○○
Corrosion Resistance	●●●●●

CORE ATTRIBUTES

Product Name	Elastech heat
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Electric Conductive	Yes
Stainless	No
Load capacity Static	160 kg
Temperature range (Minimum)	-30 °C
Temperature range (Maximum)	250 °C
Overall weight	0.35 kg

WHEEL

Tread hardness	soft
Body material	Aluminium
Tread Material Mix	Damping, heat resistant
Bearing	Dry bearing bush
Threadguards	Without threadguard
Diameter	100 mm
Tread width	35 mm
Axle Hole Diameter	8 mm
Hub Length	45 mm
Hardness of tread (A)	75 Shore A

© Copyright 2026 TENTE International GmbH


ELASTECH HEAT

IDG100x35-Ø8 (DSG)

EAN 4031582382594

BETTER MOBILITY. BETTER LIFE.

Product Drawings



© Copyright 2026 TENTE International GmbH