PRODUCT INFORMATION

OMIKRON TWIN

9951FTP400P41-400 TFR

EAN 4031582480764



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●●○
Movement noise	●●●○○
Attrition	●●●●○
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Omikron twin
Type	Swivel caster with directional lock
Load capacity at 1.8 mph	24250.82 lb
Electric conductive	no
Stainless	no
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	22.44 in
Overall weight	544.51 lb

HOUSING

Housing Material	Cast iron, or iron forged, heavy
Fork shape	Twin wheel housing
Swivel bearing	Deep-groove ball thrust roller bearing
Offset	3.54 in
Swivel radius	6.69 in
Swivel interference	13.39 in
Lubrication nipple	1

WHEEL

Body material	Casting
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	With threadguard
Diameter	15.75 in
Tread width	3.15 in
Hardness of tread (A)	92 Shore A

FITTING

Fitting type	Square plate
Plate length	15.75 in
Plate width	15.75 in
Plate hole length (Maximum)	13.39 in
Plate hole width (Maximum)	13.39 in
Plate hole diameter	0.87 in

© Copyright 2026 TENTE International GmbH


OMIKRON TWIN


9951FTP400P41-400 TFR

EAN 4031582480764

BETTER MOBILITY. BETTER LIFE.

Product Drawings





© Copyright 2026 TENTE International GmbH