PRODUCT INFORMATION

# ALPHA

## 3470BOG100P62 TFR

EAN 4031582392968

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

### PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●●○ |
| Movement Noise | ●●●○○ |
| Attrition | ●●●●● |
| Corrosion Resistance | ●●●●● |

### CORE ATTRIBUTES

| | |
|---|---|
| Product Name | Alpha |
| Type | Swivel castor |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 125 kg |
| Electric Conductive | No |
| Stainless | No |
| Load capacity Static | 250 kg |
| Temperature range (Minimum) | -40 °C |
| Temperature range (Maximum) | 280 °C |
| Overall Height | 128 mm |
| Overall weight | 0.67 kg |

### HOUSING

| | |
|---|---|
| Housing Material | Steel sheet, heavy |
| Fork shape | Broad |
| Swivel Bearing | Two ball races |
| Housing Color | Blue passivated |
| Offset | 40 mm |
| Swivel radius | 90 mm |
| Swivel interference | 180 mm |

### WHEEL

| | |
|---|---|
| Body material | Plastic thermoset, heat-resistant |
| Tread Material Mix | Identical with wheel body |
| Bearing | Dry bearing bush |
| Axle | Screwed with nut |
| Diameter | 100 mm |
| Tread width | 35 mm |
| Hardness of tread (D) | 85 Shore D |

### FITTING

| | |
|---|---|
| Fitting type | Small rectangular plate |
| Plate length | 105 mm |
| Plate width | 80 mm |
| Plate hole length (Minimum) | 77 mm |
| Plate hole length (Maximum) | 80 mm |
| Plate hole width (Maximum) | 60 mm |
| Plate hole diameter | 9 mm |

© Copyright 2026 TENTE International GmbH


# ALPHA

## 3470BOG100P62 TFR


EAN 4031582392968

**Product Drawings**

3470U00100P62-neu




Platte 3470-080P62-105x80




© Copyright 2026 TENTE International GmbH