PRODUCT INFORMATION

OMIKRON TWIN

9951FTP400P41-400 TFR

EAN 4031582480764



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●●○
Movement Noise	●●●○○
Attrition	●●●●○
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Omikron twin
Type	Swivel castor with directional lock
Load capacity at 3 km/h	11000 kg
Electric Conductive	No
Stainless	No
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall Height	570 mm
Overall weight	246.98 kg

HOUSING

Housing Material	Iron forged, heavy
Fork shape	Twin wheel housing
Swivel Bearing	Deep-groove ball thrust roller bearing
Offset	90 mm
Swivel radius	170 mm
Swivel interference	340 mm
Lubrication nipple	1

WHEEL

Body material	Cast iron
Tread Material Mix	PUR casted premium
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	With threadguard
Diameter	400 mm
Tread width	80 mm
Hardness of tread (A)	92 Shore A

FITTING

Fitting type	Square plate
Plate length	400 mm
Plate width	400 mm
Plate hole length (Maximum)	340 mm
Plate hole width (Maximum)	340 mm
Plate hole diameter	22 mm

© Copyright 2026 TENTE International GmbH


OMIKRON TWIN


9951FTP400P41-400 TFR

EAN 4031582480764

BETTER MOBILITY. BETTER LIFE.

Product Drawings





© Copyright 2026 TENTE International GmbH