PRODUCT INFORMATION

PLATE

P10-40x19 / 10 TFR

EAN 4031582393880



Image may differ from the original product

PERFORMANCE

Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Plate
Type	Accessory
Load capacity at 3 km/h	40 kg
Electric Conductive	No
Stainless	No
Load capacity Static	80 kg
Overall Height	10 mm
Overall weight	0.03 kg

FITTING

Fitting type	Stem with U-shaped plate
Plate length	40 mm
Plate width	19 mm
Plate hole length (Maximum)	32 mm
Plate hole width (Maximum)	32 mm
Plate hole diameter	4 mm

© Copyright 2026 TENTE International GmbH