PRODUCT INFORMATION

ELASTECH

IEP 300x55-Ø20 HL66

EAN 4031582319781

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Tread hardness	soft
Body material	Aluminum
Tread material	Elastic tire, black, vulcanized
Bearing	Precision ball bearing
Wheel color	Jet black (similar RAL9005)
Threadguards	Without threadguard
Diameter	11.81 in
Tread width	2.17 in
Axle hole diameter	0.79 in
Hub length	2.6 in
Body width	2.17 in
Hardness of tread (A)	68 Shore A

PERFORMANCE

Roll Performance	●●○○○
Movement noise	●●●●●
Attrition	●●●○○
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Elastech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	1322.77 lb
Load capacity at 3.7 mph	1058.22 lb
Electric conductive	no
Stainless	no
Load capacity Static	2645.54 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	185 °F
Overall weight	8.58 lb

© Copyright 2026 TENTE International GmbH


ELASTECH

IEP 300x55-Ø20 HL66

EAN 4031582319781

Order number 00834703

Product Drawings




© Copyright 2026 TENTE International GmbH

ELASTECH

IEP 300x55-Ø20 HL66

EAN 4031582319781

Order number 00332793



© Copyright 2026 TENTE International GmbH