PRODUCT INFORMATION

E-DRIVE OPTIMA

EDOAUFF125P60 24V fuer optima

BETTER MOBILITY. BETTER LIFE.

PERFORMANCE

Roll Performance	●●●●○
Movement noise	●●●●○
Attrition	●●●○○
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	E-Drive optima
Type	Drive Unit
Electric conductive	no
Stainless	no
Temperature range (Minimum)	41 °F
Temperature range (Maximum)	104 °F
Overall width	7.48 in
Overall weight	8.8 lb

HOUSING

Housing Material	Electric
Fork shape	Drive
Housing Color	Blue passivated

WHEEL

Body material	Polyamide
Tread material	Elastic tire, non-marking, vulcanized
Bearing	Flanged wheel
Wheel color	Silver gray (RAL7001)
Diameter	4.92 in
Body width	1.57 in
Hardness of tread (A)	63 Shore A

FITTING

Fitting type	Rectangular plate
Plate length	3.94 in
Plate width	3.74 in
Plate hole length (Maximum)	2.36 in
Plate hole width (Maximum)	3.94 in
Plate hole diameter	0.35 in

© Copyright 2026 TENTE International GmbH