PRODUCT INFORMATION

NOVATECH

ITB 250x55-Ø35 HL60

EAN 4031582397994



Image may differ from the original product

WHEEL

Body material	Aluminium
Tread Material Mix	PUR casted premium
Bearing	Bore with keyway
Wheel Color	Honey yellow (RAL1005)
Threadguards	Without threadguard
Diameter	250 mm
Tread width	55 mm
Axle Hole Diameter	35 mm
Hub Length	60 mm
Body width	55 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

PERFORMANCE

Roll Performance	●●●●○
Movement Noise	●●●○○
Attrition	●●●●○
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Novatech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	1200 kg
Load capacity at 6 km/h	1000 kg
Electric Conductive	No
Stainless	No
Load capacity Static	2000 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall weight	1.83 kg

© Copyright 2026 TENTE International GmbH


NOVATECH

ITB 250x55-Ø35 HL60

EAN 4031582397994

Order number 00861408

Product Drawings



© Copyright 2026 TENTE International GmbH