PRODUCT INFORMATION

# AGILA

2477PJH075P30-11

EAN 4031582323733



Image may differ from the original product

## PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●○○ |
| Movement noise | ●●●●○ |
| Attrition | ●●●○○ |
| Corrosion resistance | ●●●○○ |

## CORE ATTRIBUTES

| | |
|---|---|
| Product name | Agila |
| Type | Swivel caster with total lock |
| Standard | EN12530 - Devices Castors |
| Load capacity at 1.8 mph | 165.35 lb |
| Electric conductive | no |
| Stainless | no |
| Load capacity Static | 330.69 lb |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 140 °F |
| Overall height | 3.94 in |
| Overall width | 1.69 in |
| Overall weight | 0.62 lb |

## HOUSING

| | |
|---|---|
| Housing Material | Steel sheet, medium |
| Fork shape | Broad |
| Swivel bearing | Two ball races |
| Housing Color | Blue passivated |
| Offset | 0.94 in |
| Swivel radius | 3.15 in |
| Swivel interference | 6.3 in |
| Dome diameter | 1.69 in |

## WHEEL

| | |
|---|---|
| Body material | Polypropylene |
| Tread material | Thermoplastic rubber |
| Bearing | Plain bearing |
| Wheel color | Silver gray (RAL7001) |
| Threadguards | With threadguard |
| Diameter | 2.95 in |
| Tread width | 0.98 in |
| Body width | 0.98 in |
| Hardness of tread (A) | 87 Shore A |

## FITTING

| | |
|---|---|
| Fitting type | Bolt hole |
| Bolt hole diameter | 0.43 in |
| Hint | Castors can be mounted with standard screws of any length. |

© Copyright 2026 TENTE International GmbH


# AGILA

2477PJH075P30-11

EAN 4031582323733

Order number 00003939

**Product Drawings**






© Copyright 2026 TENTE International GmbH