PRODUCT INFORMATION

# AGILA

## 2477PJP075P40

EAN 4031582050431

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

### PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●○○ |
| Movement noise | ●●●●○ |
| Attrition | ●●●○○ |
| Corrosion resistance | ●●●○○ |

### CORE ATTRIBUTES

| | |
|---|---|
| Product name | Agila |
| Type | Swivel caster with total lock |
| Standard | EN12530 - Devices Castors |
| Load capacity at 1.8 mph | 165.35 lb |
| Electric conductive | no |
| Stainless | no |
| Load capacity Static | 330.69 lb |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 140 °F |
| Overall height | 3.94 in |
| Overall width | 1.69 in |
| Overall weight | 0.75 lb |

### HOUSING

| | |
|---|---|
| Housing Material | Steel sheet, medium |
| Fork shape | Broad |
| Swivel bearing | Two ball races |
| Housing Color | Blue passivated |
| Offset | 0.94 in |
| Swivel radius | 3.15 in |
| Swivel interference | 6.3 in |
| Dome diameter | 1.69 in |

### WHEEL

| | |
|---|---|
| Body material | Polypropylene |
| Tread material | Thermoplastic rubber |
| Bearing | Precision ball bearing |
| Wheel color | Silver gray (RAL7001) |
| Threadguards | With threadguard |
| Diameter | 2.95 in |
| Tread width | 0.98 in |
| Body width | 0.98 in |
| Hardness of tread (A) | 87 Shore A |

### FITTING

| | |
|---|---|
| Fitting type | Square plate |
| Plate length | 2.36 in |
| Plate width | 2.36 in |
| Plate hole length (Minimum) | 1.5 in |
| Plate hole length (Maximum) | 1.89 in |
| Plate hole width (Minimum) | 1.5 in |
| Plate hole width (Maximum) | 1.89 in |
| Plate hole diameter | 0.25 in |

© Copyright 2026 TENTE International GmbH


# AGILA


2477PJP075P40


EAN 4031582050431

Order number 00004470

**Product Drawings**






© Copyright 2026 TENTE International GmbH