PRODUCT INFORMATION

DURATECH

TOP082x75-Ø20

EAN 4031582452396



Image may differ from the original product

WHEEL

Body material	Polyamide, heavy
Tread Material Mix	Identical with wheel body
Bearing	Precision ball bearing
Threadguards	Without threadguard
Diameter	82 mm
Tread width	75 mm
Axle Hole Diameter	20 mm
Hub Length	77 mm
Hardness of tread (D)	75 Shore D
Bearing type	6204

PERFORMANCE

Roll Performance	●●●●●
Movement Noise	●●●○○
Attrition	●●●●●
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Duratech
Type	Wheel
Load capacity at 3 km/h	750 kg
Electric Conductive	No
Stainless	No
Load capacity Static	1500 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall weight	0.5 kg


© Copyright 2026 TENTE International GmbH


DURATECH

TOP082x75-Ø20

EAN 4031582452396

Product Drawings





© Copyright 2026 TENTE International GmbH